



Working for You... Corning Precision

Corning® Digital Hot Plates and Stirrers



Corning's new hot plates, stirrers, and stirring hot plates are made with the same durability and quality Corning has been putting into Pyrocera® top products since 1964.

- ▶ **Precise liquid temperatures and stirring speeds**

Temperature accuracy within $\pm 2^{\circ}\text{C}$ and stirring speeds at $\pm 5\%$ of the speed setting you choose.

- ▶ **Digital displays**

Indicate when set temperature and stirring speeds are reached. Facilitate repeatability of standard operating procedures.

- ▶ **Safety indicators**

Power button and hot top indicators warn if unit is plugged in or is too hot to touch.

- ▶ **Angled front panel and large knobs**

Minimizes damage from spills and puts controls right at your fingertips.

- ▶ **Optional external temperature controller**

Assures temperature accuracy of the liquid as opposed to the plate top. No more constant monitoring of temperature.

CORNING

Corning® Digital Hot Plates, Stirrers and Stirring Hot Plates

All models include Pyroceram® top and a two year warranty.

Hot Plates

Cat. No.	Model Number	Voltage	Temp. Range	Top Plate Size
6796-400D	PC-400D	230V/50Hz	5-550°C	5" x 7" (12.7 x 17.8 cm)
6796-600D	PC-600D	230V/50Hz	5-550°C	10" x 10" (25.4 x 25.4 cm)

Stirrers

Cat. No.	Model Number	Voltage	Stir Range	Top Plate Size
6796-410D	PC-410D	230V/50Hz	60-1150 RPM	5" x 7" (12.7 x 17.8 cm)
6796-610D	PC-610D	230V/50Hz	60-1150 RPM	10" x 10" (25.4 x 25.4 cm)

Stirring Hot Plates

Cat. No.	Model Number	Voltage	Temp./Stir Range	Top Plate Size
6796-420D	PC-420D	230V/50Hz	5-550°C/60-1150RPM	5" x 7" (12.7 x 17.8 cm)
6796-620D	PC-620D	230V/50Hz	5-550°C/60-1150RPM	10" x 10" (25.4 x 25.4 cm)

Accessories

Cat. No.	Description
6795PR*	Temperature Controller for digital hot plates and stirring hot plates
6970SR	Stir Bar Retriever
6795KIT	Accessory Kit (includes 6795PR - External temperature controller, 440129 - Support rods, 18," 6970SR - Stir bar retriever)
440129	Stainless Steel Support Rod - two 9" (45.7 cm) rods, 5/16" diameter. Rods can be screwed together to 18"
400084	Stainless Steel Support Rod - 12" (30.5 cm), 5/16" diameter.
440140†	Boss Head Clamp for use with 5/16" support rod and holding rod
440141	Holding Rod - thermocouple, stainless steel

*Temperature controllers are not available for use with stirrer only units.

†Bosshead clamps to support rod, holding rod connects to bosshead. Temperature controller slides into holding rod.




PC-400D



PC-410D



PC-420D



Hot Plate Accessories

Hot Plate Accessories
From left to right:
440129 - Support Rod
440141 - Holding Rod
440140 - Boss Head Clamp
6970SR - Stir Bar Retriever
6795PR - Temperature Controller



For additional product or technical information, please visit www.corning.com/lifesciences or contact your local Corning sales office listed below.

CORNING

Corning Incorporated Life Sciences

Tower 2, 4th Floor
900 Chelmsford St.
Lowell, MA 01851
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

Worldwide Support Offices

ASIA / PACIFIC

Australia
t 61 2-9416-0492
f 61 2-9416-0493

China
t 86 21-3222-4666
f 86 21-6288-1575

Hong Kong
t 852-2807-2723
f 852-2807-2152

India
t 91-124-235 7850
f 91-124-401 0207

Japan
t 81 (0) 3-3586 1996/1997
f 81 (0) 3-3586 1291/1292

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6733-6511
f 65 6861-2913

Taiwan
t 886 2-2716-0338
f 886 2-2716-0339

EUROPE

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA

Brasil
t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico
t (52-81) 8158-8400
f (52-81) 8313-8589